

TECHSPEC® 12.5mm Diameter, Reflective ND Filter Kit (14 Filters)



Stock #64-348 3-5 DAYS

- 1 + **A\$614.40**

ADD TO CART

Qty 1+
A\$614.40

Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Angle of Incidence (°):
0

Substrate: ☐
Float Glass

Filters Included :
[0.1](#), [0.15](#), [0.2](#), [0.3](#), [0.4](#), [0.5](#), [0.6](#), [0.7](#), [0.9](#), [1.0](#), [1.3](#), [1.5](#),
[2.0](#), [2.5](#)

Coating: Surface 1: Inconel
Thickness (mm): 1.60 Nominal
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%): 80
Wavelength Range (µm): 0.4 - 0.7

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View