

TECHSPEC[®]

12.5mm H x 25mm L x -12.5mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC[®] Illumination Grade PCV Cylinder Lenses

Stock #68-052 3-5 DAYS



1



A\$99.20

ADD TO CART

Qty 1-5

A\$99.20

Qty 6+

A\$79.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
-12.50

Substrate: ☐
[NSF11](#)

Coating:
Uncoated

Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 2500
Back Focal Length BFL (mm): -13.9
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 4.51
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -9.81
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View