

TECHSPEC® 125mm, Side Drive, Standard Top, English Stage



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Standard-Top Model)



Stock **#66-453** [CONTACT US](#)

- 1 +

A\$878.40

ADD TO CART

Qty 1-2

A\$878.40

Qty 3+

A\$766.72

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:

Lead Screw
Drive Orientation: Side Drive
Type: English
Stage Size (mm): 125 x 125
Travel (inches): 1
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 20
Mounting Threads: (21) 1/4-20, (8) 2-56, (4) 6-32
Stage Size (inches): 4.92 x 4.92
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant