

12.5mm Square, 0° AOI, Hot Mirror



Hot Mirrors

Stock #62-623 3-5 DAYS



1



A\$60.80

ADD TO CART

Qty 1-9

A\$60.80

Qty 10+

A\$54.24

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):
0.00

Coating:
Hot Mirror, 0°

Substrate: ☐
[BOROFLOAT®](#)

Reflection (%):

>95, 750 - 1150nm
Dimensions (mm): 12.5 x 12.5
Surface Quality: 80-50
Thickness (mm): 1.10
Transmission (%): >90, 425 - 675nm
Type: Shortpass Filter
Dimensional Tolerance (mm): ±0.5
Coating Specification: Surface 1: 0° Hot Mirror Surface 2: None
Wavelength Range (nm): 425 - 1150
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
