

12.5µm Aperture Diameter, Mounted, Precision Pinhole



12.5µm Aperture Diameter, Mounted, Precision Pinhole, #56-277

Stock **#56-277** 3-5 DAYS



1



A\$136.00

ADD TO CART

Qty 1-5

A\$136.00

Qty 6+

A\$120.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Mounted

Outer Diameter (mm):
25 +0.4/-0.000

Construction:
Stainless Steel

Fixed Aperture Diameter (µm):

12.5
Thickness (mm): 0.01 Nominal
Aperture Tolerance (µm): ±5
Mount Thickness (mm): 1.25 ±0.05
Aperture Centration (µm): ±125

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant