

127mm Clear Aperture, 2 Arcsec, Aluminum Retroreflector



Stock **#49-671** CLEARANCE 3-5 DAYS

-

1

+

A\$11,072.00

ADD TO CART

Qty 1+
A\$11,072.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec):
2.00

Clear Aperture CA (mm):
127.0

Coating:
Enhanced Aluminum (450-650nm)

Diameter (mm):
166.70

Exiting Wavefront Accuracy:
1.2λ

Substrate:  BOROFLOAT®
Surface Quality: 80-50
Mounting Threads: (7) ¼-20, (6) M6 x 1.0
Type: Retroreflector
Dimensional Tolerance (mm): ±1.6
Image Orientation: Left-Handed
Ray Deviation (°): 180
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View