


TECHSPEC® 12.7mm Dia Protected Silver, 4-6λ Mirror



Stock **#36-040** 3-5 DAYS

- 1 +

A\$44.80

ADD TO CART

Qty 1-5
A\$44.80
Qty 6+
A\$34.40
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.70 ±0.25

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 11.70
Edges: Ground, 0.5mm Maximum Edge Chip
Thickness (mm): 2.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Damage Threshold, By Design: ☐ 0.5 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant