

12.7mm Dia. UHR Broadband Dielectric Mirror, 750-1100nm



Stock #17-497 CLEARANCE 3-5 DAYS

-

1

+

A\$375.92

ADD TO CART

Qty 1+
A\$375.92

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.70 +0.00/-0.10

Surface Flatness (P-V):
λ/10

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Surface Quality:
10-5

Coating Specification:
R_{abs} >99.9% @ 750 - 1100nm (45°, s-pol)
R_{abs} >99.9% @ 750 - 1100nm (45°, p-pol)

Coating: UHR Dielectric Mirror (750-1000nm)
Coating Type: Dielectric
Angle of Incidence (°): 45
Clear Aperture CA (mm): 9.20
Edges: Ground
Parallelism (arcmin): <3
Thickness (mm): 6.35 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 750 - 1100

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View