

TECHSPEC® 12.7mm Dia., Uncoated, IR Ultrafast Thin Window



Stock #11-752 3-5 DAYS

- 1 + **A\$164.00**

ADD TO CART

Qty 1-5
A\$164.00
Qty 6+
A\$147.60
Volume Pricing
Request Quote

Get Product Downloads



Coating:
Uncoated

Diameter (mm):
12.70 +0.00/-0.10

Substrate: ▢
[Fused Silica](#) IR Grade

Index of Refraction n_d :

1.458
Surface Quality: 20-10
Thickness (mm): 1.00 ±0.10
Type: Ultrafast Window
Bevel: Protective as needed
Clear Aperture (%) : 90
Transmitted Wavefront, P-V: λ/6
Abbe Number (v_d): 67.8
Parallelism (arcsec): ≤30
Wavelength Range (nm): 200 - 3500
Fused Silica Grade: 7979 0G
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View