

12.7mm Dia. x 1mm High Efficiency Window



Stock **#39-279** [CONTACT US](#)

⊖ 1 ⊕

A\$34.40

ADD TO CART

Qty 1-5
A\$34.40
Qty 6+
A\$27.60
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Bevel:
Protective as needed

Clear Aperture (%):
≥90

Clear Aperture CA (mm):

11.43
Diameter (mm): 12.70 ±0.76
Thickness (mm): 1.00 ±0.25
Coating: BBAR (425-700nm)
Coating Specification: R _{avg} ≤0.5% @ 425 - 700nm
Edges: Ground
Substrate: Float Glass
Surface Quality: 80-50
Transmission (%): 96.9 Average (typical)
Type: Protective Window
Wavelength Range (nm): 425 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant