

# 12.7mm, ISP Optics Germanium Equilateral Prism | GE-EP-12

See More by [ISP Optics](#)



Stock #19-711 3-5 DAYS

-

1

+

A\$2,232.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| A\$2,232.00                   |
| Qty 6+                        |
| A\$1,785.60                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Coating:  
Uncoated

Substrate: ☐  
Germanium (Ge)

Surface Quality:  
60-40

|                                               |
|-----------------------------------------------|
| <b>Type:</b><br>Equilateral Prism             |
| <b>Dimensional Tolerance (mm):</b><br>±0.25   |
| <b>Angle Tolerance (arcmin):</b><br>±10       |
| <b>Clear Aperture (%):</b><br>85              |
| <b>Length of Hypotenuse (mm):</b><br>12.70    |
| <b>Length of Legs (mm):</b><br>12.70          |
| <b>Wavelength Range (nm):</b><br>2000 - 14000 |
| <b>Wavelength Range (µm):</b><br>2 - 14       |
| <b>Surface Flatness (P-V):</b><br>2λ          |
| <b>Model Number:</b><br>ZC-EP-12              |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |