

1.28mm FL CS-Mount, Manual Iris, Wide Angle Lens



1.28mm FL CS-Mount, Manual Iris, Wide Angle Lens, #62-046

Stock **#62-046** 3-5 DAYS

- 1 + **A\$1,128.00**

ADD TO CART

Qty 1+
A\$1,128.00
Volume Pricing
Request Quote

Get Product Downloads

Iris Option: Variable
Length (mm): 65.00
Maximum Diameter (mm): 36.0
Weight (g): 110.00
Horizontal Field of View, 1/3" Sensor: 125°

Maximum Image Circle (mm): 6.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 1.28
Maximum Sensor Format: 1/3"
Working Distance (mm): 100 - ∞
Mount: CS-Mount
Aperture (f/#): f/1.8 - Closed
Distortion (%): <3
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 223: Contains SVHC(s)
Certificate of Conformance: View

