

TECHSPEC® 12mm Dia. x 12mm FL VIS-EXT, Inked, Double-Convex Lens



Stock **#89-150-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 +

A\$89.60

ADD TO CART

Qty 1-9
A\$89.60
Qty 10+
A\$80.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.00 ±0.025

Back Focal Length BFL (mm):
10.79

Effective Focal Length EFL (mm):

12.00
Coating: VS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.85
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.41
Radius R₁=R₂ (mm): 15.34
Clear Aperture CA (mm): 11.00
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View