

TECHSPEC® 12mm EFL Unmounted, RKE Precision Eyepiece



TECHSPEC® RKE® Precision Eyepieces

Stock **#66-208** 3-5 DAYS

- 1 + **A\$177.60**

ADD TO CART

Qty 1-24

A\$177.60

Qty 25+

A\$128.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Distortion (%):
5 (Specified @ 0.7 Field)

Effective Focal Length EFL (mm):
12.00

Eye Relief (mm):
10.70

Field Stop Diameter (mm):

9.7
Apparent Field (°): 45.00
Back Focal Length BFL (mm): 5.81
Center Air Spacing (mm): 0.569
Lateral Color, 0.7 Field : 0.016
Total Length, Glass Only (mm): 10.43
Type: Unmounted
Spot Size (µm): 4/13 (On-Axis/0.7 Field)
Housing Length (mm): N/A
Image Distance (mm): 5.768
Manufacturer: Edmund Optics®

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View