

Ti:Sapphire Flat Top Beam Shaper 12mm | π Shaper 12_12_TiS_HP

See More by [AdlOptica](#)



Stock #14-279 [CONTACT US](#)

-

1

+

A\$15,392.00

ADD TO CART

Qty 1-4
A\$15,392.00
Qty 5+
A\$13,851.20
Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm): 800
Diameter (mm): 42.00
Entrance Beam Diameter, 1/e ² (mm): 12.0 - 12.1
Model Number:

πShaper 12_12_TIS_HP
Length (mm): 358.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <530
Wavelength Range (nm): 700 - 900
Style: Flat Top
Damage Threshold, By Design: ☐ 3000 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 12.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant