

12" Diameter, Parabolic Reflector



Stock #53-875 3-5 DAYS

- 1 +

A\$100.80

ADD TO CART

Qty 1-10
A\$100.80
Qty 11+
A\$90.72
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ Aluminum

Diameter (inches): 12.0

Diameter (mm): 304.80

Effective Focal Length EFL (inches): 3.0

Effective Focal Length EFL (mm): 76.20
Radius of Curvature (mm): 152.40
Coating: Uncoated
Coating Type: Uncoated
Center Hole Diameter (inches): 0.75
Height (mm): 72.39
Thickness (inches): 0.04
Thickness (mm): 1.02
Type: Parabolic Mirror
Weight (kg): 0.267

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
