

[See all 1 Products in Family](#)

## 12" x 11.5" 0°, Glossy, 3M Light Control Film



Stock #52-385 **12 In Stock**

⊖ 1 ⊕ A\$286<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$286.40 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Specialty Window **Type:**

### Physical & Mechanical Properties

304.80 **Length (mm):**

12 x 11.5 **Dimensions (inches):**

304.8 x 292.1      **Dimensions (mm):**

0.021      **Thickness (inches):**

0.50      **Thickness (mm):**

292.10      **Width (mm):**

## Optical Properties

Polycarbonate      **Substrate:**

## Environmental & Durability Factors

-40 to +120      **Operating Temperature (°C):**

## Regulatory Compliance

[Compliant](#)      **RoHS 2015:**

[View](#)      **Certificate of Conformance:**

[Compliant](#)      **Reach 240:**

## Product Details

- Ideal for Privacy Viewing
- Contrast Enhancement and Improved Sunlight Readability
- Reduces Unwanted Reflections

3MLight Control Film is a high-performance plastic, containing closely spaced microlouvers. These louvers simulate a tiny venetian blind, blocking out unwanted ambient light and controlling the direction of display light. The results of these features are higher contrast enhancement, improved readability in sunlight, and the ability to direct light, as well as restricting readability to a single viewer for privacy.

## Technical Information

