

13mm Travel, 0.01mm Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#33-727** **1 In Stock**

⊖ 1 ⊕ A\$145⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-9 | A\$145.60 each |
| Qty 10-24 | A\$131.04 each |
| Need More? | Request Quote |

Product Downloads

General

Metric **Type:**
Mtutoyo **Manufacturer:**

Physical & Mechanical Properties

13 **Travel (mm):**
Graduation (mm):

| | |
|-----------------|----------------------------------|
| 0.01 | |
| 9.5 | Stem Diameter (mm): |
| Plain/Spherical | Stem/Spindle: |
| 9.5 | Stem Length (mm): |
| 5 | Spindle Diameter (mm): |
| 15.5 | Min. Spindle Length (mm): |
| 13 | Max. Diameter (mm): |
| 62 | Overall Length (mm): |

Hardware & Interface Connectivity

| | |
|-------------------|-----------------------|
| Metric Micrometer | Type of Drive: |
|-------------------|-----------------------|

Regulatory Compliance

| | |
|----------------------------------|------------------------------------|
| Exempt | RoHS 2015: |
| View | Certificate of Conformance: |
| Contains SVHC(s) | REACH 241: |

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential. Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

