

# 13mm Travel, Metric Micrometer, Thru-Hole Ball Bearing Stage



32mm/1.25" Side drive stage and its X-Y-Z configuration

Stock **#37-958** [CONTACT US](#)

-

1

+

**A\$833.60**

ADD TO CART

Qty 1+

A\$833.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:  
Linear (X)

Guide System:  
Ball Bearing

Type of Drive:  
Metric Micrometer

Drive Orientation:  
Side Drive

Type:  
English

|                                                                   |
|-------------------------------------------------------------------|
| <b>Stage Size (mm):</b><br>44.4 x 44.4                            |
| <b>Travel (mm):</b><br>13                                         |
| <b>Length (mm):</b><br>55.37                                      |
| <b>Construction:</b><br>Aluminium Stage                           |
| <b>Graduation (mm):</b><br>0.01                                   |
| <b>Height (inches):</b><br>0.75                                   |
| <b>Height (mm):</b><br>19.1                                       |
| <b>Load Capacity, Normal (lbs):</b><br>25                         |
| <b>Note:</b><br>Thru-Hole                                         |
| <b>Stage Size (inches):</b><br>1.75 x 1.75                        |
| <b>Straight Line Accuracy (inches):</b><br>0.00008/inch of travel |
| <b>Weight (lbs):</b><br>0.5                                       |
| <b>Thrust Capacity, T<sub>a</sub> (lbs):</b><br>10                |
| <b>Thrust Capacity, T<sub>b</sub> (lbs):</b><br>5                 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---