

104mm Max. Aperture, Iris Diaphragm



Stock #32-610 3-5 DAYS

- 1 + **A\$681.60**

ADD TO CART

Qty 1-4
A\$681.60
Qty 5+
A\$601.28
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
5.0

Maximum Aperture (mm):
104.0

Outer Diameter (mm):
140.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 19.80
Number of Leaves: 16.00
Thickness (mm): 11.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)
