

1.5" LED Spot Light, White

See More by [Advanced Illumination](#)



Stock #66-815

CONTACT US

-

1

+

A\$686.40

ADD TO CART

Qty 1+

A\$686.40

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:

White

Diameter (mm):

38.00

Model Number:

SL2420-WHI-24

Length (mm):

54.00

Operating Temperature (°C): 0 to 65
Working Distance (mm): 100.00
Intensity Control Option: No
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10 Edge to Edge (Dependent on Working Distance)
Number of LEDs: 20.00
Number of Channels: 1.00
Field Coverage (mm): 43.00
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant