

TECHSPEC® 15 x 15mm UV Enhanced Aluminum, λ/4 Mirror



Stock **#45-726** 3-5 DAYS

- 1 +

A\$84.00

ADD TO CART

Qty 1-5

A\$84.00

Qty 6+

A\$67.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: 
BOROFLOAT®

Back Surface:
Commercial Polish

Surface Quality:

60-40
Dimensions (mm): 15.0 x 15.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 2.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Length (mm): 15.00
Width (mm): 15.00
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant