

15 x 21.21 x 2mm Elliptical Beamsplitter 50R/50T



Stock #27-608 CLEARANCE 3-5 DAYS

-

1

+

A\$39.92

ADD TO CART

Qty 1+
A\$39.92

Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture (%):
80.00

Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR ¼λ MgF₂ @ 550nm

Dimensional Tolerance (mm):
±0.25

Dimensions (mm):
15.0 x 21.21

Major Axis (mm):
21.21

Minor Axis (mm): 15.00
Reflection (%): 50.00
Substrate: ☐ N-BK7
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.25
Transmission (%): 50.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
