


150 x 150mm, 2.000mm Spacing, White Ivory Distortion Target



Stock #63-992 [CONTACT US](#)

-

1

+

A\$4,560.00

ADD TO CART

Qty 1-4
A\$4,560.00
Qty 5+
A\$4,333.28
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Reflective First Surface Chromium
R_{abs} = 50% ±5% @ 550nm

Dot Diameter (mm):
1.000

Dot Spacing (mm):

2.000
Substrate: White Ivory Soda Lime Glass
Optical Density OD (Average): >3.0
Overall Accuracy (mm): ±0.002
Pattern Size (mm): 150 x 150
Dimensions (inches): 7 x 7
Surface Quality: 40-20
Thickness (mm): 3.20
Type: Chrome on White Ivory Glass
Dot Diameter Tolerance (mm): ± 0.002
Dot Spacing Tolerance (mm): ± 0.002 Center to Center
NIST Certification: Serialized NIST Traceable Certificate Included
Flatness (inches): 0.001

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
