


TECHSPEC® 1500nm 25.0mm Diameter, OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock **#84-678** 3-5 DAYS

⊖ 1 ⊕

A\$217.60

ADD TO CART

Qty 1-5

A\$217.60

Qty 6+

A\$184.96

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-On Wavelength (nm): 1,500.00
Substrate:  Fused Silica (Corning 7980)
Coating: Traditional Coated
Rejection Wavelength (nm): 1200 - 1460
Surface Quality: 40-20
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.1
Transmission (%): >85
Transmission Wavelength (nm): 1550 - 2000
Type: Longpass Filter
Clear Aperture (%): 80
Transmitted Wavefront, P-V: λ/4
Cut-On Tolerance (%): ±2
Slope Factor (%): 3.00
Coating Specification: Surface 1: Multi-Layer Dielectric Surface 2: MgF ₂
Wavelength Range (nm): 1200 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View