

150mm Dia x 300mm Focal Length, PCX Condenser Lens



Stock #27-509 3-5 DAYS

-

1

+

A\$288.00

ADD TO CART

Qty 1-10
A\$288.00
Qty 11+
A\$252.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
150.00 +0.0/-0.5

Effective Focal Length EFL (mm):
300.00 @ 587.6nm

Back Focal Length BFL (mm):
284.00

Coating:
Uncoated

Substrate: N-BK7
Surface Quality: 120-80
Center Thickness CT (mm): 24.40
Edge Thickness ET (mm): 5.06
Radius R₁ (mm): 155.10
Clear Aperture CA (mm): 146
f#: 2.00
Numerical Aperture NA: 0.25
Type: Condenser Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View