

150mm Dia x 360mm FL Alum. Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock #90-971 3-5 DAYS

⊖ 1 ⊕ **A\$1,080.00**

ADD TO CART

Qty 1-10
A\$1,080.00
Qty 11+
A\$952.80
Volume Pricing
Request Quote

Get Product Downloads

Substrate: □
[BOROFLOAT®](#)

Coating:
Protected Aluminum (400-700nm)

Coating Specification:
R_{avg} >85% @400 - 700nm

Coating Type:

Metal
Center Hole Diameter (mm): 40.0
Height (mm): 70.0
Inner Diameter (mm): 141
Outer Diameter (mm): 150.00 +0.0/-0.5
Type: Specialty Mirror
Wavelength Range (nm): 400 - 700
Distance to Focal Point f_1 (mm) : 22.5
Distance to Focal Point f_2 (mm): 360

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View