

Red 625nm, MicroBrite Ultra High Intensity Bar Light

See More by [Advanced Illumination](#)



Stock #18-541 3-5 DAYS

- 1 + **A\$940.80**

ADD TO CART

Qty 1+

A\$940.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
Red

Input Voltage (V):
24V

Model Number:
AL295-150625IC

Operating Temperature (°C):
0 - 60

Dimensions (mm):
165.6 x 20.1 x 20.1

Wavelength (nm): 625.00
Weight (g): 68.9
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Area Light
Maximum Input Current: 0.34A
Illumination Mode: Constant
Environmental Rating: IP50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)