

150mm Travel, Motorized Linear Stage

See More by [Zaber™](#)



150mm Travel, Motorized Linear Stage, #15-289

Stock **#15-289** 3-5 DAYS

-

1

+

A\$4,472.00

ADD TO CART

Qty 1+
A\$4,472.00
Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Recirculating Ball Linear Guide

Type of Drive:
Precision Lead Screw

Type:
Universal (Metric & English)

Stage Size (mm):

65 x 361.2
Travel (mm): 150
Accuracy (µm): 50 (unidirectional)
Backlash (µm): <18
Encoder: No
Height (mm): 35.8
Load Capacity (kg): 50
Manual Control/ LED Indicators: Yes
Manufacturer: Zaber Technologies Inc.
Note: Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232 connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to control simultaneously.
Operating Temperature (°C): 0 - 50
Power Supply: Power Supply Required and Sold Separately. USA: #15-294 Europe: #15-294 Japan: #23-662 Korea: #33-773 China: #15-294
Repeatability (µm): <3
Resolution (µm): 0.49609375
Speed (mm/s): 0.0003 to 280
Thrust (N): <75
Type of Motor: 2-Phase Stepper
Weight (kg): 1.4
Computer Interface: USB with #15-295 RS-232 with #15-297
Maximum Operating Current (mA): <1450

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant