

TECHSPEC® 15mm Dia., 0.67 NA, Uncoated 1550nm NIR Aspheric Lens



Stock #17-415 3-5 DAYS

-

1

+

A\$512.00

ADD TO CART

Qty 1-5
A\$512.00
Qty 6+
A\$409.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):
11.25 @ 1550nm

Numerical Aperture NA:
0.67

Back Focal Length BFL (mm):

7.88 @ 587.6nm
Substrate: N-SF6
Aspheric Design Wavelength (nm): 1550
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 13.5
Edge Thickness ET (mm): 1.5
Center Thickness CT (mm): 5.00 ±0.1
f/#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Conjugate Distance: Infinite
Asphere Figure Error, @ 632.8nm: 0.4λ RMS and 2λ PV
Power (diopters): 88.89

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View