

TECHSPEC[®] 15mm Length, S-Mount Extension Tube



Stock #63-957 20+ In Stock

-

1

+

A\$44^{.80}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$44.80 each
Qty 5-9	A\$40.00 each
Qty 10-25	A\$37.28 each
Need More?	Request Quote

Product Downloads

General

Extension Tube

Type:

Extension Tube (Fixed)

Function:

Physical & Mechanical Properties

15.0

Extension Length (mm):

19.0	Total Length (mm):
16.0	Outer Diameter (mm):
10.0	Clear Aperture CA (mm):

Threading & Mounting

S-Mount	Thread Type:
---------	--------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.