

TECHSPEC® 15mm Max Aperture Motorizable Iris



High Performance Motorizable Iris



Stock **#34-289** 3-5 DAYS

- 1 +

A\$121.60

ADD TO CART

Qty 1-4

A\$121.60

Qty 5+

A\$107.36

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.2

Maximum Aperture (mm):

15.0
Outer Diameter (mm): 24.0
Construction: Brass-Spring Steel
Number of Leaves: 12
Thickness (mm): 5.00
Pitch Diameter (mm): 21.3

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)

