

**TECHSPEC® 15mm, Uncoated, N-BK7 Right Angle Prism**



N-BK7 Right Angle Prisms

Stock **#32-332** [CONTACT US](#)



1



**A\$97.60**

ADD TO CART

Qty 1-5

**A\$97.60**

Qty 6+

**A\$87.84**

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[N-BK7](#)

Surface Quality:

60-40

|                                             |
|---------------------------------------------|
| <b>Type:</b><br>Right Angle Prism           |
| <b>Dimensional Tolerance (mm):</b><br>±0.1  |
| <b>Angle Tolerance (arcmin):</b><br>±2      |
| <b>Bevel:</b><br>Protective bevel as needed |
| <b>Length of Hypotenuse (mm):</b><br>21.20  |
| <b>Length of Legs (mm):</b><br>15.00        |
| <b>Image Orientation:</b><br>Left-Handed    |
| <b>Ray Deviation (°):</b><br>90             |
| <b>Wavelength Range (nm):</b><br>350 - 2200 |
| <b>Surface Flatness (P-V):</b><br>λ/4       |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |