

TECHSPEC<sup>®</sup> 15mm VIS 0° Coated Dove Prism



Stock #49-426 3-5 DAYS

-

1

+

A\$212.80

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| A\$212.80                     |
| Qty 6+                        |
| A\$191.52                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Coating:  
VIS 0° (425-675nm)

Substrate:   
[N-BK7](#)

Height (mm):  
15.0

Length (mm):

|                                                                                       |
|---------------------------------------------------------------------------------------|
| 62.50                                                                                 |
| <b>Surface Quality:</b><br>60-40                                                      |
| <b>Type:</b><br>Dove Prism                                                            |
| <b>Dimensional Tolerance (mm):</b><br>±0.13 Legs, ±0.25 Length                        |
| <b>Angle Tolerance (arcmin):</b><br>2.00                                              |
| <b>Bevel:</b><br>Protective bevel as needed                                           |
| <b>Image Orientation:</b><br>Left-Handed                                              |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm                 |
| <b>Ray Deviation (°):</b><br>0                                                        |
| <b>Wavelength Range (nm):</b><br>425 - 675                                            |
| <b>Surface Flatness (P-V):</b><br>λ/8 (Entrance and Exit Faces)                       |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>5 J/cm² @ 532nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |