

TECHSPEC® 15mm VIS-EXT, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock #11-288 3-5 DAYS

- 1 + **A\$412.80**

ADD TO CART

Qty 1-5
A\$412.80
Qty 6+
A\$323.20
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:

MS-EXT (400-640nm)
Coating Specification: R _{avg} <0.5% @ 400 - 640nm
Construction: Cube
Dimensions (mm): 15.0 x 15.0 x 15.0 ±0.1
Reflection/Transmission Ratio (R/T): 50/50
Substrate:  N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 400 - 640
[Ts-Tp]: <6%
Absolute Transmission (%): 45 ±10

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View