

TECHSPEC® 15X Arcturus® HeNe Beam Expander



15XHeNe Fixed Beam Expander, #58-209

Stock #58-209 3-5 DAYS

- 1 +

A\$896.00

ADD TO CART

Qty 1-4

A\$896.00

Qty 5+

A\$792.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):
0

Coating:
BBAR (450-750nm)

Design Wavelength DWL (nm):
633

Entrance Aperture (mm):

Exit Aperture (mm): 27
Expansion Power: 15X
Focus Range: 1.2m - ∞
Substrate: ☐ Optical Glass
Length (mm): 120.50
Mounting Threads: C-Mount
Type: Beam Expander
Weight (g): 461
Housing Diameter (mm): 50
Transmitted Wavefront, P-V: <λ/4 @ 633nm for Input Beam ≤1mm
Coating Specification: R _{abs} <0.4% @ 630 - 670nm R _{avg} <0.6% @ 450 - 750nm
Wavelength Range (nm): 450 - 750
Style: Fixed Magnification
Divergence Adjustment: Non-Rotating Optics

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View