

16.0mm FL, No IR-Cut Filter, f/2, Micro Video Lens



Stock **#64-108** 3-5 DAYS

[Similar Products](#)

- 1 +

A\$94.40

ADD TO CART

Qty 1-49
A\$94.40
Qty 50+
A\$75.20
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
14.40

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
14.0

Maximum Image Circle (mm):

6.00
Horizontal Field of View @ Max Sensor Format: 17
Resolution, On-Axis: 75 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 65 lp/mm @ 20% Contrast
Resolution, Full Field: 60 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 16.00
Maximum Sensor Format: 1/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
Distortion (%): -2.50 @ Full Field
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
