

16mm MegaPixel Fixed Focal Length Lens



MegaPixel Fixed Focal Length Lenses

Stock **#56-788** 3-5 DAYS

[Similar Products](#)

- 1 +

A\$480.00

ADD TO CART

Qty 1+
A\$480.00
Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm):
125.00

Iris Option:
Variable

Length (mm):
28.20

Horizontal Field of View, 1/2" Sensor:
22.70°

Filter Thread:

M30.5 x0.50
Maximum Diameter (mm): 33.50
Weight (g): 60.00
Maximum Rear Protrusion (mm): 0.90
Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 16.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View