

# 1700mW, 808nm Laser ZQ1, 30°



Stock #19-442 3-5 DAYS

- 1 + **A\$7,280.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| A\$7,280.00                   |
| Qty 10+                       |
| A\$6,552.00                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads



**Operating Temperature (°C):**  
-10 to +50

**Output Power (mW):**  
1700

|                                                               |
|---------------------------------------------------------------|
| <b>Dimensions (inches):</b><br>6.26 x 2.57 x 2.03 (L x W x H) |
| <b>Wavelength (nm):</b><br>808.00                             |
| <b>Weight (g):</b><br>690                                     |
| <b>Working Distance (mm):</b><br>below 3.3ft (1m)             |
| <b>Laser Class - IEC:</b><br>3B                               |
| <b>Storage Temperature (°C):</b><br>-40 to +85                |
| <b>Modulation Frequency (kHz):</b><br>200                     |
| <b>Style:</b><br>Homogeneous Line                             |
| <b>Output Type:</b><br>Free Space                             |
| <b>Type of Laser:</b><br>Diode                                |
| <b>Laser Class - CDRH:</b><br>IIIb                            |
| <b>Color:</b><br>Near Infrared                                |
| <b>Connector:</b><br>5 Pins, M12                              |
| <b>Fan Angle (°):</b><br>30.00                                |
| <b>Focus Range:</b><br>100mm up to 10,000mm                   |
| <b>Input Voltage (V):</b><br>12 - 24                          |
| <b>Diameter of Laser Head (inches):</b><br>0.79               |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |