

1.74mm FL, IR-Cut Filter at 650nm, f/2.8, Micro Video Lens



Stock **#66-881** CLEARANCE CONTACT US

-

1

+

A\$49.60

ADD TO CART

Qty 1+
A\$49.60

Volume Pricing
Request Quote

Get Product Downloads

Length (mm): 19.60
Maximum Diameter (mm): 21.0
Maximum Image Circle (mm): 4.50
Horizontal Field of View @ Max Sensor Format: 114.4
Resolution, On-Axis: 124 lp/mm @20% Contrast

Resolution, 0.7 Field: 87 lp/mm @ 20% Contrast
Resolution, Full Field: 30 lp/mm @ 20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 1.74
Maximum Sensor Format: 1/4"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mbunt)
Aperture (f/#): f/2.8
Distortion (%): -60 @Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

Reach 205: Compliant
Certificate of Conformance: View