

1.75" Max. Opening, Soft Jaw Pliers



Stock **#59-900** **5 In Stock**

-

1

+

A\$95^{.20}

ADD TO CART

Volume Pricing	
Qty 1+	A\$95.20 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

44.45 (1.75")	Tip to Tip Distance, Open (mm):
---------------	---------------------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Non-Marring Cushioned Tips
- Screw-In Cushioned Tip Design
- Replacement Tips Available

The slip joint design utilized in these pliers is ideal for handling optics, camera-lens assemblies, and other delicate components. Jaw openings range from 1" to 2.75" (dependent on model). Jaws feature screw-in plastic cushions to protect fine knurling and delicate finishes. Tool body is laminated and handles are covered with rolled vinyl to ensure proper grip.