

[See all 5 Products in Family](#)

## 17mm Dia x 85mm FL, Grade 1, Plano-Convex Lens



Stock #74-993 CLEARANCE **1 In Stock**

- 1 + A\$16<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>A\$16.40</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Plano-Convex Lens **Type:**

#### Physical & Mechanical Properties

17.00 **Diameter (mm):**

#### Optical Properties

85.00 **Effective Focal Length EFL (mm):**

**f#:**

5.00

Numerical Aperture NA:

0.10

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

