

17mm Dia x 85mm FL, Grade 1, Plano-Convex Lens



Stock **#74-993** CLEARANCE **1 In Stock**

-

1

+

A\$16^{.40}

ADD TO CART

Volume Pricing	
Qty 1+	A\$16.40 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

17.00

Diameter (mm):

Optical Properties

85.00

Effective Focal Length EFL (mm):

f/#:

5.00	
	Numerical Aperture NA:
0.1	
Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

