

1800 Grooves/mm, 30mm Square, VIS Holographic Grating



Reflective Holographic Gratings

Stock **#55-265** 3-5 DAYS

- 1 + **A\$360.00**

ADD TO CART

Qty 1+

A\$360.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):
1800

Wavelength Range (nm):
400 - 700

Dimensions (mm):
30.0 x 30.0 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 30.00
Substrate:  Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Wavelength: VIS
Width (mm): 30.00
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%) : 81
Peak Efficiency Avg, Typical (%) : >65

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
