

[All Products](#) / [Imaging Lenses](#) / [Zoom Lenses](#) / [Varifocal Imaging Lenses](#)

[See all 3 Products in Family](#)

1.8mm - 3.6mm Focal Length, Varifocal Video Lens



1.8mm-3.6mm FL, Varifocal Video Lens, #55-254

Stock **#55-254** 3-5 DAYS



1



A\$472.00

ADD TO CART

Qty 1+

A\$472.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):
1236 - 332

Length (mm):
51.00

Maximum Diameter (mm):
37.4

Horizontal Field of View, 1/3" Sensor:
144.2° - 79.4°

Maximum Rear Protrusion (mm):
0.0

Type: Varifocal Lens
Focal Length FL (mm): 1.80 - 3.6
Maximum Sensor Format: 1/3"
Working Distance (mm): 200 - ∞
Mount: CS-Mount
Aperture (f#): f/1.6 - f/16
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

