

1.8mm Dia, 1550nm DWL, 0.23mm WD, Uncoated, GRIN Lens



Stock **#64-532** 3-5 DAYS

-

1

+

A\$92.00

ADD TO CART

Qty 1-10
A\$92.00
Qty 11+
A\$81.60
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 1.80 +0.00/-0.01
Effective Focal Length EFL (mm): 1.75
Substrate: ☐ Aluminosilicate Glass Embedded with Silver Ions
f/#: 0.97

Numerical Aperture NA: 0.51
Coating: Uncoated
Type: Gradient Index Lens
Wavelength Range (nm): 1310 - 1550
Clear Aperture (%): 90.00
Gradient Constant (mm⁻¹): 0.358
Index of Refraction n_d - Center of Lens: 1.616
Length (mm): 4.01
Pitch: 0.23
Surface Quality: 40-20
Working Distance (mm): 0.23
Working Distance Tolerance (mm): ±0.01
Length Tolerance (%): ±5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View