


TECHSPEC[®] 18mm Dia Protected Silver, 4-6λ Mirror



Stock #36-042 3-5 DAYS

-

1

+

A\$44.80

ADD TO CART

Qty 1-5

A\$44.80

Qty 6+

A\$34.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
18.00 ±0.25

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 17.00
Edges: Ground, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Damage Threshold, By Design: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant