

TECHSPEC[®] 1mm, Uncoated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock #45-947 [CONTACT US](#)

-

1

+

A\$128.00

ADD TO CART

Qty 1-5

A\$128.00

Qty 6+

A\$115.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[N-BK7](#)

Surface Quality:

20-10

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 1.40
Length of Legs (mm): 1.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/4

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View