

1" Travel, Eng Micrometer, Thru-Hole 1.75" Stage



Stock #53-857 3-5 DAYS

- 1 + **A\$1,734.40**

ADD TO CART

Qty 1+
A\$1,734.40

Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Digital Micrometer (English)

Drive Orientation:
Center Drive

Type:
English

Stage Size (mm): 44.4 x 44.4
Travel (inches): 1
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Graduation (inches): 0.00005
Load Capacity, Normal (lbs): 25
Load Capacity, T_a (lbs): 10
Load Capacity, T_b (lbs): 5
Note: Thru-Hole
Stage Size (inches): 1.75 x 1.75
Straight Line Accuracy (inches): 0.00008 per inch of travel
Weight (lbs): 0.8

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View