

1" x 1" (100 lp/mm), Ronchi Ruling



Stock **#58-780** 3-5 DAYS

- 1 +

A\$542.40

ADD TO CART

Qty 1-4
A\$542.40
Qty 5+
A\$516.32
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Frequency (lp/mm):
100

Substrate:
Float Glass

Optical Density OD (Average): 3.00
Dimensions (inches): 1 x 1
Surface Quality: 60-40
Thickness (mm): 1.50
Type: Metric
Dimensional Tolerance (mm): ± 0.02
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View